






Specifications

Coupling:	Threaded coupling
Shell material:	Brass with Nickel Plate
Insert material:	bakelite
Contact material:	copper Silver Plate/Nickel
Termination:	Solder
Mating cycle:	500
Cable diameter:	-20°C +85°C



Ordering Information

XD - GX20 - NP - *

No. of Pin
2~10 Pin
Contact
Type
F=Female
M=Male

NO. of contacts	芯数	2	3	4	5	6	7	8	9	10	12	14	15
Rated current (A)	额定电流	15A	15A	10A	10A	10A	10A	10A	10A	5A	5A	5A	5A
Operation limit voltage(AC.V.rms) 工作电压(AC.V) 分钟		250V	250V	200V	200V	200V	200V	200V	200V	200V	200V	200V	200V
Withstanding voltage(AC.V.rms) 1 minute 耐压		1500	1500	1500	1000	1000	1000	1000	1000	1000	1000	1000	1000
Insulation resistance (MΩ)	绝缘阻抗	1500	1500	1500	1000	1000	1000	1000	1000	1000	1000	1000	1000
Contact resistance (mΩ)	接触阻抗	3	3	3	3	3	3	3	3	3	3	3	3

			GENErl TOLERANCE	制 图 DRAWING	 深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd				
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL	产品名称 TITLE	GX20 航空插头 公头	版本 REV.	A	
1	初版发行		X.XX ±0.20 X.XXX ±0.10	比 例 SCALE	产品料号 PART NO.	XD-GX20-NP-M	单位 UNITS	mm	
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投 影 Projection		材 料 MATERIAL	页 次 SHEET	1/1	