






◆ SCHEMATIC




◆ P.C.B LAYOUT



Poles(N) A Dimension(mm)

01	2.87
02	4.12
03	5.41
04	6.66
05	7.93
06	9.20
08	11.74
10	14.28
TOLERANCE:±0.1mm	

◆ STRUCTURE



◆ MATERIAL

Part Name	Material	Finished
Base	PPS UL94 V0	Black
Cover	PPS UL94 V0	Black
Actuator	Nylon UL94 V0	White
Movable	Beryllium	3μ " Gold
Terminal Contact	Brass	3μ " Gold
Terminal	Brass	3μ " Gold
Tape	Polyimide	Amber

HY-DSHP XX TS

Finish G-Full Gold S-Contat Gold plated
Terminal S:SMD H:Straight

Actuator T(Tape sealed) S (Low profile W/0 Tape) L (Extension)

HP:Haif-Pitch IC:IC PV:Piano WB:WB

_____		new		2015/5/3		A		瀚源
ECN BO.		DESCRIPTION.		DATE.		REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	HY-DSHPXXTS	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.	±0.25
			MODEL NAME	HY-DSHPXXTS			X.x	±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx
							ANGULAR	±3°
							FILE.NO.	