



SCHEMATIC

1. 电气参数: 48VDC 5A 5000Cycle;
2. 操作环境温度: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$;
3. 线材外观光滑, 平整, 绝缘护套不得有划伤残缺等不良现象;
4. 耐压: 250Vac 1分钟;
5. 连接器拉脱力: 单根线 $>35.6\text{N}$;
6. DC JACK插拔力: $(3 \sim 30)\text{N}$;
7. 环保要求: 符合Rohs/Reach;
8. 带" * "尺寸为品质重点管控尺寸;
9. 电线胶股: $(1 \sim 4)$ 股;



8	Heat shrinkable tube	Ø2.0x10mm	3
7	Adhesive	WTS-80305（双面打胶）	0.07g
6	WIRE	W-UL1061#22-0088-WT	1
5	WIRE	W-UL1061#22-0088-RD	1
4	WIRE	W-UL1061#22-0088-BK	1
3	Connector Base	A2502-H03-1-V0	1
2	Connector Terminal	A2501-T21P2	3
1	DC JACK	DC-005CAΦ1.65-SU 平片2.5	1
NO.	PART NAME	PART DESCRIPTION	QTY

TOLERANCE UNLESS SPECIFIED

UP TO 5mm: ±0.1	ANGULAR ±1°	2	2021.6.24	更新图纸	WM
ABOVE 5mm: ±0.2		1	2021.3.23	更新图纸	WM
		NO	DATE	REVISIONS	BY APPD

TITLE : DC JACK		UNIT : MM	ROHS COMPLIANT	DWN
MODEL: DC-005CAΦ1.65-ASSY-004		SCALE: 4:1	CHK'D	
HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司			APPD	
			PRO.AGL:	