





P.C.B LAND DIMENSION




CIRCUIT DIAGRAM



NOTE

1. RATING : DC 12V 50mA
2. CONTACT RESISTANCE : $100\text{m}\Omega$ MAX
3. GENERAL TOLERANCE : ± 0.2
4. MANUFACTURING SPECIFICATION WOULD BE ACCORDANCE WITH WT0158

					TOLERANCE UNLESS SPECIFIED								
					UP TO 5mm:±0.1	ANGULAR	1						
					ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS			BY	APPD
5	STEM	PA6T	1	BLACK	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
4	COVER	BRASS	1	CuSn-PLATED	MODEL: TC-00204A-048C				SCALE: 1:1	COMPLIANT	CHK'D		
3	CONTACT	SUS	1	Ag-PLATED	HAOYU(HONGKONG)LIMITED 皓 宇(香 港)有 限 公 司				APPD		PRO.AGL: 		REV :A1
2	TERMINAL	BRASS	3	Ag-PLATED									
1	BASE	PA6T	1	BLACK									
NO.	PART NAME	MATERIAL	QTY	FINISHING									