






P.C.B LAYOUT
TOLERANCE:±0.05

Ordering Information:

A2502WR-XP - **
1 2

1.Part NO.

2.Style:

(Blank): TYPE 1

2: TYPE 2

SPECIFICATIONS:

Current Rating: 3A AC,DC

Voltage Rating: 250V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 10mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: 800V AC/minute

Pin Material: Brass/Tin over Nickel

Material: Nylon 66,UL94V-0(White)

Ordering Information & Dimensions

Part NO.	Dimensions(mm)	
	A	B
A2502WR-2P	2.50	7.50
A2502WR-3P	5.00	10.00
A2502WR-4P	7.50	12.50
A2502WR-5P	10.00	15.00
A2502WR-6P	12.50	17.50
A2502WR-7P	15.00	20.00
A2502WR-8P	17.50	22.50
A2502WR-9P	20.00	25.00
A2502WR-10P	22.50	27.50
A2502WR-11P	25.00	30.00
A2502WR-12P	27.50	32.50
A2502WR-13P	30.00	35.00
A2502WR-14P	32.50	37.50
A2502WR-15P	35.00	40.00

CJTconn CHANGJIANG CONNECTORS CO.,LTD.			
Unit	Scale	Sheet	TITLE
mm	4:1	1 of 1	2.50mm PITCH 90° WAFER
DRWN	CHKD	APPR	
Chengbiao Ye	Diankui Wan	Jack Yin	DRAWING NO. A2502WR-XP
General Tolerances		THIRD ANGLE PROJECTION	
A4	CHANGE THE DRAWING	2023.10.30	REV A4
A3	CHANGE THE DRAWING	2020.12.25	
A2	CHANGE THE DRAWING	2019.01.17	DRAWING NO. A2502WR-XP
A1	APPEARANCE CHANGE	2018.09.07	
A0	NEW RELEASE	2009.05.10	REV A4
REV	DESCRIPTION	DATE	