








SCHEMATIC



P.C.B LAYOUT



ACTION FIGURE

					TOLERANCE																
					UNLESS SPECIFIED			2015.03.9	接触片改良			Hunter.H									
					UP TO 5mm:±0.1	ANGULAR		2013.05.10	ECN1305001			Hunter.H									
					ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS			BY	APPD								
5	PB-12R10 SPRING	0.25mm SUS	1						TITLE:PUSH SWITCH		UNIT : MM	ROHS	DWN								
4	PB-12R10 CONTACT△	0.06mm PBS	1	Ag CLAD					MODEL: PB-12R10A-W		SCALE: 2:1	COMPLIANT	CHK'D								
3	PB-12R10 KNOB	POM	1	WHITE					HOOYA ELECTRONIC CO. LTD 皓宇电子有限公司							APPD					
2	PB-12R10 COVER	PBT/PC	1	BLACK/WHITE/NATURAL																	
1	CASE	PA66/BRASS	1	BLACK/Ag PLATED																	
NO.	PART	NAME	MATERIAL	QTY	FINISHING								PRO.AGL:		REV : F						