

REV.	EQN. NO.	APPD.
A		

材料数据

材质:

Pin: 黄铜, C3604

电镀:

镀锡: $2\mu\text{m}/80\mu$ "镍, $5\mu\text{m}/200\mu$ 锡

镀金: $2\mu\text{m}/80\mu$ "镍, 0.8μ "金

阻燃等级: PPS UL94V-0

电气性能

额定电流: 3Amps/contact max.

接触电阻: $\leq 20\text{m}\Omega$ /contact

绝缘电阻: $\geq 1000\text{M}\Omega$ at V=100V





工作电压: 60VAC/DC

物理性能:

机械寿命: min 500

工作温度范围: -40°C to $+105^{\circ}\text{C}$

焊接温度: $+255^{\circ}\text{C}$



MT	X	X	X	X	XX	XXXX
Specifications	Pitch (mm)	Insulator Type	Angel Options	No. of Positions	Pin Length Options	
A=Public seat	A=1.27	I=Single row	D=180°	XX positions	1000=10.00mm	
B=Female seat	B=1.778	2=Double row	R=90°			
	C=2.00	3=Three row	S=SLT			
	D=2.54		I=IC			

X. ±0.30	X.° ±5°	UNITS mm	NAME (INTENDED USE)	MINTRON CO., LTD.
.X ±0.20	.X° ±2°	MATL	PART NO. (INTENDED USE)	
.XX ±0.10	.XX° ±1°	FINISH	Socket Connectors 2.54mm L=10.0mm Ø0.60 常规型	
.XXX ±0.05	.XXX° ±0.5°		APPD: SUNNY	DWG NO.:
PIN CONNECTOR	QTY	CHKD: LISA	DR: ZOE	MTAD1-DXX10000
2016-03-29				SCALE 1/1
				SHEET 1/1
				REV. A