






SCHEMATIC



P.C.B LAND DIMENSION

					TOLERANCE UNLESS SPECIFIED								
					UP TO 5mm: ±0.1	ANGULAR	1						
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD	
4	CONTACT FOOT	BRASS	4	Ag-Plated	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
3	COVER	IRON	1	Ni-Plated	MODEL: TC-00104-130C				SCALE: 1:1	COMPLIANT	CHK'D		
2	BUTTON	PA66	1		 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司					APPD			
1	HOUSING	PA66	1										
NO.	PART	NAME	MATERIAL	QTY	FINISHING						PRO.AGL:	 	REV:A0