

材料数据

材质:

Pin: 黄铜, C3604

电镀:

镀金: 2 μm/80 μ" 镍, 0.8 μ" 金

阻燃等级: PPS UL94V-0

电气性能

额定电流: 1Amps/contact max.

接触电阻: ≤20mΩ/contact

绝缘电阻: ≥1000MΩ at V=100V





工作电压: 60VAC/DC

物理性能:

机械寿命: min 500

工作温度范围: -40° C to +105° C

焊接温度: +255° C



P. C. B LAYOUT

MT	X	X	X	-	X	XX	XXX
Specifications A=Public seat B=Female seat	Pitch (mm) A=1.27 B=1.778 C=2.00 D=2.54	Insulator Type code 1=Single row 2=Double row 3=Three row	Angel Options D=180° R=90° S=CNT I=IC	No. of Positions XX positions	Pin Length Options 0820=8.20mm		

X. ± 0.30		X.° ± 5°	UNITS mm	NAME(INTENDED USE)		MINTRON CO.,LTD.			
.X ± 0.20		.X° ± 2°	MAT'L	PART NO.(INTENDED USE)					
.XX ± 0.10		.XX° ± 1°	FINISH	TITLE:					
.XXX ± 0.05		.XXX° ± 0.5°		Double row socket connector 1.27mm*H1.90 L=8.20mm					
PIN CONNECTOR			QTY	APPD: SUNNY	DWG NO.: MTA2-DXX0820				
			CHKD: LISA				SCALE	SHEET	REV.
			DR: ZOE 2024-01-22				1/1	1/1	A
									