




REV.	ECN. NO.	APPD.
A		



P. C. B LAYOUT

材料数据

材质:

Pin外壳: 黄铜, C3604
内爪 (4爪): 镀铜, C17200
电镀 (外壳):
镀锡: 2 μm/80 μ"镍, 5 μm/200 μ锡
镀金: 2 μm/80 μ"镍, 0.8 μ"金
电镀 (内爪): 2 μm/80U"镍底, 0.8 μ"金
适配公针φ: 0.40mm/0.60mm
阻燃等级: PBT UL94V-0

电气性能

额定电流: 3Amps/contact max.
接触电阻: ≤20mΩ/contact
绝缘电阻: ≥1000MΩ at V=100V
工作电压: 60VAC/DC

物理性能:

平均插入力 φ0.50: <270g
平均拔出力 φ0.50: >90g
机械寿命: min 500
工作温度范围: -40° C to +105° C
焊接温度: +200° C

MT	X	X	X	XX	XXXX
Specifications A=Public seat B=Female seat	Pitch (mm) A=1.278 B=2.54	Dip spacing 0= No 1=1.27mm 2=2.54mm 3=7.62mm 4=10.16mm 5=15.24mm	Angle Options D=180° R=90° S=SMT 11=C-180度 12=C-90度 13=I-C-SMT	No. of Positions XX positions	Pin Length Options 0743=7.43mm

X.	± 0.30	X.°	± 5°	UNITS	mm	NAME (INTENDED USE)	MINTRON CO., LTD.
.X	± 0.20	.X°	± 2°	MATL		PART NO. (INTENDED USE)	Dual in-line Socket 2.54mm L=7.43mm H=3.0 P=7.62mm
.XX	± 0.10	.XX°	± 1°	FINISH		APPD: SUNNY	DWG NO.: MTBD3-1180743
.XXX ± 0.05	.XXX° ± 0.5°			QTY		CHKD: LISA	SCALE 1/1
FEMALE CONNECTOR						DR: ZOE	SHEET 1/1
						2016-03-18	REV. A