








P.C.B LAND
DIMENSION



REFERENCE DRAWING

					TOLERANCE UNLESS SPECIFIED										
					UP TO 5mm: ± 0.1	ANGULAR $\pm 1^\circ$	1								
					ABOVE 5mm: ± 0.2		NO	DATE	REVISIONS			BY	APPD		
5	STEM	Silica gel	1	Blue/White	TITLE: TACT SWITCH			UNIT : MM	ROHS COMPLIANT	DWN					
4	COVER	SUS	1	Ni plating	MODEL: TS-1110U3-051D			SCALE: 1:1		CHK' D					
3	CONTACT	SUS	1	Ag plating	 HAOYU (HONGKONG) LIMITED 皓 宇(香 港)有 限 公 司								APPD		
2	CASE	PA9T	1	Black											
1	TERMINAL	BRASS	4	Ag plating									PRO. AGL:	 	REV :A0
NO.	PART NAME	MATERIAL	QTY	FINISHING											