







AFTER MATING



RECOMMENDED PCB LAYOUT (TOP VIEW)

THICKNESS 0.60MM; DEFAULT TOLERANCE: ±0.05

A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

USB TYPE-C PIN ASSIGNMENTS

					TOLERANCE UNLESS SPECIFIED								
					UP TO 5mm:±0.1	ANGULAR							
					ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS			BY	APPD
4	FRONT SHELL	STEEL	1	Ni-PLATED	TITLE: USB JACK				UNIT : MM	ROHS COMPLIANT	DWN		
3	MID PLATE	STEEL	1	SN-PLATED	MODEL: USB-307				SCALE: 1:1		CHK'D		
2	CONTACTS	BRASS	24	Au-PLATED	 HAOYU(HONGKONG)LIMITED 皓 宇(香 港)有 限 公 司				APPD				
1	HOUSING	LCP(UL94V-0)	1	BLACK/ORANGE									
NO.	PART	NAME	MATERIAL	QTY	FINISHING				PRO.AGL:  				REV :A0