








SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $160\pm 50\text{gf}/250\pm 80\text{gf}$ (依客户需求而定) .
- 6.life test: 30,000 cycles.
- 7.Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 8.Sign"* "is importance dimension.



SCHEMATIC



P.C.B LAYOUT

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	1	2024.2.27	△1	按产品更正材质		TQF	
5	STEM	PA66 △1	1	BLACK/WHITE			NO	DATE	REVISIONS			BY	APPD
4	COVER	STAINLESS IRON △1	1	Sn-PLATED	TITLE: TACT SWITCH			UNIT : MM		ROHS	DWN		
3	CONTACT	SUS △1	1	Ag-PLATED	MODEL: TC-00305-050C-CU			SCALE: 1:1		COMPLIANT	CHK'D		
2	TERMINAL	BRASS △1	1	Ag-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司					APPD			
1	BASE	PA66 △1	1	BLACK									
NO.	PART	NAME		MATERIAL	QTY	FINISHING	PRO.AGL:   REV: A1						