


SPECIFICATION



1. Rating : DC 50V 0.3A.
2. Function: 1P2T
3. Contact resistance: $\leq 100\text{m}\Omega$
4. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
5. Withstanding voltage: 250VAC .
6. Operating Force: $300\pm 150\text{gf}$
7. Life test: 10,000 cycles.
8. Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
9. Sign* * "is importance dimension.




SCHEMATIC (SHORTING) ⚠

档位切换过程1#2#3# 脚短路

外壳内部凹点处涂油



H=XXmm

P.C.B LAYOUT
BOTTOM VIEW

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A1	2022.03.04	⚠ 根据实物修正电气性能			GYW	
5	CONTACT CLIP	PBS STRIP	1	Ag CLAD			NO	DATE	REVISIONS			BY	APPD
4	TERMINAL	BRASS STRIP	3	Ag PLATED	TITLE: SLIDE SWITCH			UNIT : MM		ROHS	DWN		
3	BASE	PHENOLIC RESIN	1	NATURAL	MODEL: SS-12D07VG2 PA66			SCALE: 1:1		COMPLIANT	CHK'D		
2	FRAME	STEEL STRIP	1	Ni PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司					APPD			
1	KNOB	PA66	1	BLACK									
NO.	PART NAME	MATERIAL	QTY	FINISHING						PRO.AGL:  			REV :A1