





SCHEMATIC

SPECIFICATION

1. Rating: DC 12V 0.3A
3. Contact Resistance: $\leq 70\text{m}\Omega\text{MAX}$
4. Operating Force: $130\pm 30\text{gf}$, $160\pm 50\text{gf}$, $250\pm 80\text{gf}$
5. Life test: 50,000 cycles



P.C.B. LAYOUT

					TOLERANCE UNLESS SPECIFIED							
					UP TO 5mm: ± 0.1	ANGULAR	AO	2018.05.11	首次发行		GYW	
					ABOVE 5mm: ± 0.2	$\pm 1^\circ$	NO	DATE	REVISIONS		BY	APPD
4	TS1157A CONTACT	SUS	1	Ag PLATED	TITLE:TACT SWITCH			UNIT : MM	ROHS	DWN		
3	TS1157AD CASE	PA6T/BRASS	1	BLACK/Ag PLATED	MODEL: TS-1157AD-034CL-SU T8.3			SCALE: 8:1	COMPLIANT	CHK'D		
2	TS1157AD COVER	0.15mm SUS	1	WASHING	 HOOYA ELECTRONIC CO. LTD 皓宇电子有限公司					APPD		
1	TS1157AD KNOB	RUBBER	1	BLUE						PRO.AGL:	 	REV :A0
NO.	PART NAME	MATERIAL	QTY	FINISHING								