


REV.	ECN. NO.	APPD.
A		



材料数据

材质:

Pin外壳: 黄铜, C3604

电镀:

镀锡: 2 μ m/80 μ "镍, 5 μ m/200 μ 锡

镀金: 2 μ m/80 μ "镍, 0.8 μ "金

阻燃等级: PPS UL94V-0

电气性能

额定电流: 3Amps/contact max.

接触电阻: ≤20m Ω /contact

绝缘电阻: ≥1000M Ω at V=100V



工作电压: 60VAC/DC

物理性能:

机械寿命: min 500

工作温度范围: -40° C to +105° C

焊接温度: +255° C



P. C. B LAYOUT

MT	X	X	X	XX	XXXX
Specifications A=Public seat B=Female seat					
Pitch (mm) A=1.27 B=1.778 C=2.00 D=2.54					
Insulator Type code 1=Single row 2=Double row 3=Three row					
Angel Options D=180° R=90° S=SMT I=IC					
No. of Positions XX positions					
Pin Length Options 1000=10.00mm					

X.	± 0.30	X.°	± 5°	UNITS	mm	NAME(INTENDED USE)		MINTRON CO.,LTD.			
X	± 0.20	X°	± 2°	MAT'L		PART NO.(INTENDED USE)		TITLE: Double Row Socket Connectors 2.54mm L=10.0mm Ø0.60 常规型			
XX	± 0.10	XX°	± 1°			APPD: SUNNY		DWG NO.: MTAD2-DXX10000			
.XXX	± 0.05	.XXX°	± 0.5°	FINISH		CHKD: LISA		SCALE 1 / 1			
PIN CONNECTOR				QTY		DR: ZOE		SHEET 1 / 1			
						2016-03-29		REV. A			