




REV.	ECN. NO.	APPD.
A		



材料数据

材质:

Pin: 黄铜, C3604

电镀:

镀锡: $2\mu\text{m}/80\mu$ “镍, $5\mu\text{m}/200\mu$ 锡

镀金: $2\mu\text{m}/80\mu$ “镍, 0.8μ ” 金

阻燃等级: PPS UL94V-0

电气性能

额定电流: 1Amps/contact max.

接触电阻: $\leq 20\text{m}\Omega/\text{contact}$

绝缘电阻: $\geq 1000\text{M}\Omega$ at $V=100\text{V}$


工作电压: 60VAC/DC

物理性能:

机械寿命:min 500

工作温度范围: -40°C to $+105^{\circ}\text{C}$

焊接温度: +255°C



P.C.B LAYOUT

MT	X	X	X	—	X	XX	XXXX
Specifications A=Public seat B=Female seat	Pitch(mm) A=1, 27 B=1, 78 C=2, 00 D=2, 54	Insulator Type code 1=Single row 2=double row 3=three row	Angel Options D=180° R=90° S=SMT I=C	No. of Positions XX positions	Pin Length Options 1030=10.30mm 1284=12.84mm		

X. ± 0.30		X° ± 5°	UNITS	mm	NAME/(INTENDED USE)		MINTRON CO.,LTD.		
X ± 0.20		X° ± 2°	MATL		PART NO./(INTENDED USE)		TITLE: Double row socket connector 1.27mm*H1.90 L=10.30/12.84mm 90°		
XX ± 0.10		XX° ± 1°	FINISH		APPD: SUNNY		DWG NO.: MTAA2-RXX1284		
.XXX ± 0.05		.XXX° ± 0.5°	PIN		CHKD: LISA		SCALE SHEET REV.		
CONNECTOR		QTY		DR: ZOE		2024-01-22			
									
		1 / 1		1 / 1		A			