



B±0.25



2.50±0.10

Ø 1.20±0.05

P.C.B LAYOUT

Poles	Dimensions (mm)	
	A	B
2	2.50	7.50
3	5.00	10.00
4	7.50	12.50
5	10.00	15.00
6	12.50	17.50
7	15.00	20.00
8	17.50	22.50
9	20.00	25.00
10	22.50	27.50
11	25.00	30.00
12	27.50	32.50
13	30.00	35.00
14	32.50	37.50
15	35.00	40.00
16	37.50	42.50

8.70

7.00±0.25

3.40±0.20

0.64

A±0.20

2.50±0.10

5.80

技术指标:

1. 塑体表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25° C~85° C.
3. 额定电压: 50V, AC,DC.
4. 接触电阻: ≤0.02Ω.
5. 绝缘电阻: ≥100MΩ

APPROVALS

DATE

DRAWN

G.M.Chen

2024/10/17

CHECKED

TITLE:

2.54mm Crimp Style Connectors

APPROVALS

PART NO.

XHB-XXA

A

NEW

ECN NO.

REV.

DATE.

DESCRIPTION.

CHANGE.

CHECK.

APPRO.

TOLERANCES ARE

30~0.15
10~0.10
5~0.05

±0.30
±0.20
±0.15

ANGLE

UNIT: mm

SCALE: 1:1

SHEET 1 OF 1

PROJ

DEALON 德之隆®
ELECTRONICS CO.,LTD