



SPECIFICATIONS

Current rating: 3A AC/DC
Voltage rating: 250V AC/DC
Contact resistance: 20mΩ max.
Withstand voltage: 1000V AC/min
Insulation resistance: 1000MΩ/min.
Temperature range: -25°C~+85°C
Applicable PC board thickness: 0.063"(1.6)

Material:

Part No: 2~20
Post: Brass. Tin/plated
Base: Nylon66 UL94V-2/0



P.C.B LAYOUT

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	TITLE: Ckmtw 深圳市灿科盟实业有限公司 CHANKELEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:				
DRAWN:	DATE:	CLIENT P/N		/	
LXF	2008-04-07	UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-2501-0003	REV.	A
				WD00	