

ROHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.09.21	


Specifications(规格):

- 1.Impedance(特性阻抗) : 50Ω;
- 2.Frequency (工作频率) : DC~3GHz;
- 3.Insulation resistance(绝缘阻抗) : ≥100MΩ;
- 4.Dielectric withstand voltage (介质耐电压) : 500V AC;
- 5.Mating cycles (耐久性) : ≥25 cycles;
- 6.Temperature range(使用温度): -40℃~+105℃;



PART NO.:

XS62WM1NR-NZ05

62: H=6.25mm
70: H=7.05mm



3D View



Recommended P.C.B Layout

ANGLAR	±5°
X.	±0.50
X.x	±0.30
X.xx	±0.20
X.xxx	±0.10
UNSPECIFIED TOLERANCES	

3	Dielectric	LCP		1 PC	
2	Outer Conductor	Zinc Alloy	Tin PLATED	1 PC	
1	Center Conductor	Copper Alloy	Gold PLATED	1 PC	
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					



DESIGN	希文	VIEW:
CHECKED		UNIT: mm/in
APPROVED		SIZE: A4

MODEL TYPE:	SMB Male Connector.SMT,H=6.25mm
PART NO.:	XS62WM1NR-NZ05
DWG NO.:	X-XS62WM1NR-NZ05

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0