

A

B

C

D

E

F

G

A

B



C

D

E

F

G





SPECIFICATIONS

Current Rating: 1.0 Amps
Withstanding Voltage: AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature: -40°to+105°
Insrlator Material: Polyester
Contact Material: Phosphor bronze
Standard: PA6T
Contact Plating:Gold Flash
Max.Processing Temp: 200°C for30-60seconds
(255°C for5seconds)

尺寸对列表

H	PC	PB
4.3	4.8	4.6



RECOMMEND P. C. B LAYOUT

PCB TOLERANCE: ±0.05 (TOP VIEW)

2	接触	铜	镀金	
1	基座	PA6T	本色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	排母
料号 PART NO	HC-PM127-4.3H-2x14PS

一般公差 TOLERANCE	比列 SCALE	1:1	制图 DRAW		AhYe	审核 CHECKED	夏操云	批准 APPROVE	赵亮亮
X :±0.30 X° :±5°	单位 UNIT	MM							
X.X :±0.25 X.X° :±1°	张数 PART NO	1 OF 1							
X.XX:±0.20 X.XX° :±0.5°	版本 REV	A							

