


ROHS



3D View

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.09.21	


Specifications(规格):

- Impedance(特性阻抗) : 50Ω ;
- Frequency (工作频率) : DC~3GHz;
- Insulation resistance(绝缘阻抗) : $\geq 100M\Omega$;
- Dielectric withstand voltage (介质耐电压) : 500V AC;
- Mating cycles (耐久性) : ≥ 25 cycles;
- Temperature range(使用温度): $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$;

PART NO.:

XS70WM1NR-N025

62: H=6.25mm
70: H=7.05mm



Recommended P.C.B Layout

ANGLAR	$\pm 5^{\circ}$
X.	± 0.50
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.10
UNSPECIFIED TOLERANCES	

3	Dielectric	LCP		1 PC	
2	Outer Conductor	Zinc Alloy	Tin PLATED	1 PC	
1	Center Conductor	Copper Alloy	Gold PLATED	1 PC	
NO.	SPEC.	MATERIAL	FINISH (Contact)	Q'TY	Note
		www.helloxkb.com	www.helloxkb.com	www.xk-dq.cn	



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	希文	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.:
APPROVED		SIZE: A4	DWG NO.:
			XS70WM1NR-N025
			X-XS70WM1NR-N025
		SCALE	PAGE
		N/A	1/1
		REVISION	A0