


Current Transformer

◆ OUTLINE DIMENSION (Unit:mm):



◆ ELECTRICAL CHARACTERISTIC

NO	ITEM	MEASURED POINT	TECHNICAL DATA	REMARK
1	Normal Primary Current	Through-Core (P1-P2)	200A	
2	Normal Secondary current	1-2	5A	
3	Accuracy		1.0	Phase Displacement $\leq 120'$ Ratio Error ± 1.0
4	Primary/secondary ratio	1-2	40TS	
5	Load Resistance		$\leq 10\Omega$	
6	DC Resistance	1-2	60 Ω MAX	at 25 $^{\circ}$ C
7	Nominal working		50-60Hz	
8	operation Temperature		-20 $^{\circ}$ C to +50 $^{\circ}$ C	
9	HI-POT	P-S	3000VAC 50Hz 1mA/10s	
10	