







SPECIFICATION

1. Rating : DC 20V 6.5A.
2. Contact resistance: $\leq 50\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
4. Withstanding voltage: 250VAC .
5. Insertion and extraction force: 5-35N
5. life test: 5000 cycles.
6. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
7. Sign"* "is importance dimension.



P.C.B LAYOUT

8	包圆	BRASS	1	Sn-PLATED	TOLERANCE UNLESS SPECIFIED								
7	铁壳	FE	1	Sn-PLATED									
6	左长针	BRASS	1	Sn-PLATED	<1.5: ±0.1mm	ANGULAR ±1°							
5	右短针	BRASS	1	Sn-PLATED	>1.5~5.0: ±0.25mm								
					>5.0: ±0.3mm		NO	DATE	REVISIONS		BY	APPD	
4	右长针	BRASS	1	Sn-PLATED	TITLE: DIN SOCKET				UNIT : MM		ROHS	DWN	
3	左短针	BRASS	1	Sn-PLATED	MODEL: DIN-422				SCALE: 1:1		COMPLIANT	CHK'D	
2	后盖	PBT	1	BLACK	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司						APPD		
1	基座	PBT	1	BLACK									
NO.	PART NAME	MATERIAL	QTY	FINISHING							PRO.AGL:		REV :A0