


Current Transformer

◆ **OUTLINE DIMENSION (Unit:mm):**



◆ ELECTRICAL CHARACTERISTIC

NO	ITEM	MEASURED POINT	TECHNICAL DATA	REMARK
1	Normal Primary Current	Through-Core (P1-P2)	600A	
2	Normal Secondary current	1-2	5A	
3	Accuracy		1.0	Phase Displacement $\leq 120'$ Ratio Error ± 1.0
4	Primary/secondary ratio	1-2	120TS	
5	Load Resistance		$\leq 10\Omega$	
6	DC Resistance	1-2	55 Ω MAX	at 25℃
7	Nominal working		50-60Hz	
8	operation Temperature		-20℃ to +50℃	
9	HI-POT	P-S	3000VAC 50Hz 1mA/10s	
10	