




Recommend P.C.B LAYOUT
Tolerance:±0.05



Notes:

1.Materials:

- 1.1 Insulator Materials: PA6T,Black,UL94V-0
1.2 Contact Material: Brass

2.Electrical

- 2.1 Current Rating: 0.75A Max
2.2 Voltage Rating: 125V AC/DC
2.3 Contact Resistance: 30mΩ Max
2.4 Dielectric Withstanding Voltage: 300V AC rms
2.5 Insulation Resistance: 1000MΩ Min
2.6 Operating Temperature: -40°C~+105°C

Ordering Code

P2 C XX A - 201020 - B 1 P
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① P2:1.00mm Pitch Pin Header
② Plastic Height: C:1.00mm
③ Number of Contacts:
04=4Pin (2P~30P)
④ Series No
A: Straight Single Row DIP180°
⑤ D/E/F Length:
e.g D=2.0 E=1.0 F=2.0
D/E/F=201020
⑥ Insulator material:
B PA6T Black
⑦ Contact Plating:
1:Gold flash over Nickel
⑧ Packing
P: PE BAG

PIN	DIM A	DIM B
2P	1.00	2.00
3P	2.00	3.00
4P	3.00	4.00
5P	4.00	5.00
6P	5.00	6.00
7P	6.00	7.00
8P	7.00	8.00
9P	8.00	9.00
10P	9.00	10.00
11P	10.00	11.00
12P	11.00	12.00
13P	12.00	13.00
14P	13.00	14.00
15P	14.00	15.00
16P	15.00	16.00
17P	16.00	17.00
18P	17.00	18.00
19P	18.00	19.00
20P	19.00	20.00
21P	20.00	21.00
22P	21.00	22.00
23P	22.00	23.00
24P	23.00	24.00
25P	24.00	25.00
26P	25.00	26.00
27P	26.00	27.00
28P	27.00	28.00
29P	28.00	29.00
30P	29.00	30.00

5.0

4.0

3.0

2.0

1.0

REV.

DATE

DESCRIPTION

DRAWING

DRAWING:
FrankCHECKED:
Hu yataoAPPROVAL:
yang jie

GENERAL TOLERANCE

.X:=±0.30 .X*:±2°
.XX:=±0.20 .XX*:±1°
.XXX:=±0.10 .XXX*:±0.5°

UNIT: MM

SCALE: 1/1

SHEET: 1/1

PROJECTION:



CHIN-BAN
Electronic Technology

DESCRIPTION:
1.00mm Pitch Pin Header Single Row DIP180°

SERIES: P2CXXA Series

PART NO: P2CXXA-201020-B1P

OLD CODE:

REV: 1.0

SIZE: A4