





Recommend P.C.B LAYOUT
Tolerance:±0.05



Notes:

1.Materials:

- 1.1 Insulator Materials: PA6T,Black,UL94V-0
1.2 Contact Material: Brass

2.Electrical

- 2.1 Current Rating: 1.0A Max
2.2 Voltage Rating: 125V AC/DC
2.3 Contact Resistance: 20mΩ Max
2.4 Dielectric Withstanding Voltage: 300V AC rms
2.5 Insulation Resistance: 1000MΩ Min
2.6 Operating Temperature: -40°C~+105°C

Ordering Code

P3 C XX C - 191415 - B 1 P
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① P3:1.27mm Pitch Pin Header
② Plastic Height: C:1.00mm
③ Number of Contacts:
04=4Pin (2P~30P)
④ Series No
C: Right Angle Single Row DIP90°
⑤ D/E/F Length:
e.g D=1.9 E=1.4 F=1.5
D/E/F=191415
⑥ Insulator material:
B PA6T Black
⑦ Contact Plating:
1:Gold flash over Nickel
⑧ Packing
P: PE BAG

PIN	DIM A	DIM B
2P	1.27	2.54
3P	2.54	3.81
4P	3.81	5.08
5P	5.08	6.35
6P	6.35	7.62
7P	7.62	8.89
8P	8.89	10.16
9P	10.16	11.43
10P	11.43	12.70
11P	12.70	13.97
12P	13.97	15.24
13P	15.24	16.51
14P	16.51	17.78
15P	17.78	19.05
16P	19.05	20.32
17P	20.32	21.59
18P	21.59	22.86
19P	22.86	24.13
20P	24.13	25.40
21P	25.40	26.67
22P	26.67	27.94
23P	27.94	29.21
24P	29.21	30.48
25P	30.48	31.75
26P	31.75	33.02
27P	33.02	34.29
28P	34.29	35.56
29P	35.56	36.83
30P	36.83	38.10

5.0

4.0

3.0

2.0

1.0

REV.

DATE

DESCRIPTION

DRAWING

DRAWING:

Frank

CHECKED:

Hu yatao

APPROVAL:

yang jie

GENERAL TOLERANCE


.X:=±0.30 .X*:=±2°
.XX:=±0.20 .XX*:=±1°
.XXX:=±0.10 .XXX*:=±0.5°

UNIT: MM

PROJECTION:

SCALE: 1/1

SHEET: 1/1



DESCRIPTION:

1.27mm Pitch Pin Header Single Row DIP90°

SERIES: P3CXXC Series

PART NO: P3CXXC-191415-B1P

OLD CODE:

REV: 1.0

SIZE: A4

CHIN-BAN
Electronic Technology