







Notes:

1.Materials:

- 1.1 Insulator Materials: PA6T,Black,UL94V-0
1.2 Contact Material: Brass

2.Electrical

- 2.1 Current Rating: 1.0A Max
2.2 Voltage Rating: 125V AC/DC
2.3 Contact Resistance: 20mΩ Max
2.4 Dielectric Withstanding Voltage: 300V AC rms
2.5 Insulation Resistance: 1000MΩ Min
2.6 Operating Temperature: -40°C~+105°C

Ordering Code

P3 C XX G - 304932 - B 1 P
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① P3:1.27mm Pitch Pin Header
② Plastic Height: C:1.00mm
③ Number of Contacts:
04=4Pin (4P~60P)
④ Series No
G: Right Angle Double Row DIP90°
⑤ D/E/F Length:
e.g D=3.0 E=4.9 F=3.2
D/E/F=304932
⑥ Insulator material:
B PA6T Black
⑦ Contact Plating:
1:Gold flash over Nickel
⑧ Packing:
P: PE BAG

PIN	DIM A	DIM B
4P	1.27	2.54
6P	2.54	3.81
8P	3.81	5.08
10P	5.08	6.35
12P	6.35	7.62
14P	7.62	8.89
16P	8.89	10.16
18P	10.16	11.43
20P	11.43	12.70
22P	12.70	13.97
24P	13.97	15.24
26P	15.24	16.51
28P	16.51	17.78
30P	17.78	19.05
32P	19.05	20.32
34P	20.32	21.59
36P	21.59	22.86
38P	22.86	24.13
40P	24.13	25.40
42P	25.40	26.67
44P	26.67	27.94
46P	27.94	29.21
48P	29.21	30.48
50P	30.48	31.75
52P	31.75	33.02
54P	33.02	34.29
56P	34.29	35.56
58P	35.56	36.83
60P	36.83	38.10

5.0			
4.0			
3.0			
2.0			
1.0			
REV.	DATE	DESCRIPTION	DRAWING

DRAWING:
Frank
CHECKED:
Hu yatao
APPROVAL:
yang jie

GENERAL TOLERANCE
.X:=±0.30 .X*: =±2°
.XX:=±0.20 .XX*: =±1°
.XXX:=±0.10 .XXX*: =±0.5°

UNIT: MM
SCALE: 1/1
SHEET: 1/1



DESCRIPTION: 1.27mm Pitch Pin Header Double Row DIP90°		
SERIES:	P3CXXG Series	REV: 1.0
PART NO:	P3CXXG-304932-B1P	SIZE: A4
OLD CODE:		

CHIN-BAN
Electronic Technology