



使用温度范围 (Ambient temperature Range): -25°~+85°

适用线规 (Applicable Wires): AWG 28#~20#

适用基板厚度 Applicable PCboard thickness): 1.7mm

额定电压 (Voltage rating): 300V AC,DC

额定电流 (Current rating): 4A

接触电阻 Contact Resistance) < 0.015Ω

绝缘电阻 (Insulation Resistance): > 1000MΩ

耐压 (Withstand Voltage): 1000V/min

材料 (Material)

1. 基座: PA66 FV2
2. 插针: 黄铜

孔位	A	B
2	0	5.4
4	4.2	9.6
6	8.4	13.8
8	12.6	18.0
10	16.8	22.2
12	21.0	26.4
14	25.2	30.6
16	29.4	34.8
18	33.6	39.0
20	37.8	43.2
22	42.0	47.4
24	46.2	51.6

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	黄彬 2021.01.15	料号 PART NO.	HX-5569-2x3AW	版本 REV.
			X.±0.25	X.±2°					
			.X±0.20	.X±1°	审核 CHECK	张伟 2021.01.15	品名 TITLE	针座	页次 SHEET
			.XX±0.15	.XX±0.5°	核准 APPROVAL	罗小春 2021.01.15	客户料号 CUTM. NO.		1/1
			.XXX±0.10	.XXX±0.5°	单位 UNITS	MM	比例 1:1		



深圳市韩下电子有限公司