



Engineer Drawing



SPECIFICATIONS:

Voltage Rating: 250V AC/DC
 Current Rating: 4A AC/DC
 Withstanding Voltage: 1000V AC/min
 Temperature Range: -25°C to +85°C
 Insulation Resistance: 10mΩ Max
 Wire Range: AWG#24-#30
 Insulation O.D: 1.57mm/Max
 Qty/Reel: 10Kpcs

MATERIAL:

Terminal: Phosphor Bronze
 Plating: 80-120u" Tin plated over
 30-60u" Nickel plated

IPCW 254 T 03 X X X X X
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- | | |
|------------------|------------------|
| ① Series Type | ⑤ Material Code |
| ② Pitch: 2.54mm | ⑥ Other Code |
| ③ Connector Type | ⑦ Terminal |
| ④ Serial Code | ⑧ Other Code |
| | ⑨ Plating: T=Tin |

GENERAL
 TOLERANCES:
 X. = ±0.30
 X.X = ±0.20
 X.XX = ±0.10

NCP

www.i-ncp.com

PART NO:
 IPCW254T03 xx ET
 DRAWING NO
 IPCW254T03ET

NAME:
 2.54mm Pitch Terminal Tight
 Type AWG #24 ~ #30

SHEET 1 OF 1

UNITS:mm SCALE:1:1 REV.01