





REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行	2020-8-18			



PCB LAYOUT

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X.		X°	±3.00°
X. X	±0.35	X. X°	±2.00°
X. XX	±0.25	X. XX°	±1.00°
X. XXX	±0.15	X. XXX°	

15P	37.5
14P	35
13P	32.5
12P	30
11P	27.5
10P	25
9P	22.5
8P	20
7P	17.5
6P	15
5P	12.5
4P	10
3P	7.5
2P	5
NUMBER OF PINS	DIM. A

技术要求:

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

适应基板厚度: 1.2mm~1.6mm
温度范围: -25℃~85℃
额定电压: 250V AC/DC
额定电流: 3A
接触电阻: ≤ 0.01Ω
绝缘电阻: ≥ 1000MΩ
耐 压: 1000V AC/minute

2	PIN	N PCS	材质:黄铜,电镀:镀亮锡60u"MIN
1	Housing	1 PCS	材质:PA66 (UL94V-0),颜色:本色
NO.	NAME	Q' TY	DESCRIPTION

 深圳市韩下电子有限公司

DRAW :	黄彬	2020-8-18	TITLE: 针座		DRAW NAME: HX-2510-4A		
DESIGN:							
CHECK:	张伟	2020-8-18	SERIES: 1501 SERIES		DRAW NO.		
APPROVED	罗小春	2020-8-18	P/N:				
CUSTOMER DRAWING			REV. 1.00	SCALE N/A	UNIT: mm	SHEET: 1/1	