



使用温度范围 (Ambient temperature Range): -25°~+85°
 适用线规 (Applicable Wires): AWG 28#~20#
 适用基板厚度 Applicable PCboard thickness): 1.7mm
 额定电压 (Voltage rating): 300V AC,DC
 额定电流 (Current rating): 4A
 接触电阻 Contact Resistance) < 0.015Ω
 绝缘电阻 (Insulation Resistance): > 1000MΩ
 耐压 (Withstand Voltage): 1000V/min
 材料 (Material)
 1. 基座: PA66 FV2
 2. 插针: 黄铜

孔位	A	B
2	0	5.4
4	4.2	9.6
6	8.4	13.8
8	12.6	18.0
10	16.8	22.2
12	21.0	26.4
14	25.2	30.6
16	29.4	34.8
18	33.6	39.0
20	37.8	43.2
22	42.0	47.4
24	46.2	51.6

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	黄彬 2021.01.15	料号 PART NO.	HX-5569-2x4A	版本 REV.
			X.±0.25	X.±2°					
			.X±0.20	.X°±1°	审核 CHECK	张伟 2021.01.15	品名 TITLE	针座	页次 SHEET
			.XX±0.15	.XX°±0.5°	核准 APPROVAL	罗小春 2021.01.15	客户料号 CUTM. NO.		1/1
			.XXX±0.10	.XXX°±0.5°	单位 UNITS	MM	比例 1:1		



深圳市韩下电子有限公司