



	0	1	2	3	4	5	6	7	8	9	10	11																																									
A							REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED																																								
B							1.00		初版发行	2020-8-18																																											
C																																																					
D																																																					
E																																																					
F																																																					
G																																																					
H																																																					
PCB LAYOUT																																																					
DIM A																																																					
																																																					
																																																					
<p>适应基板厚度: 1.2mm~1.6mm 温度范围: -25°C~85°C 额定电压: 250V AC/DC 额定电流: 3A 接触电阻: ≤0.02 Ω 绝缘电阻: ≥1000MΩ 耐压: 1000V AC/minute</p>																																																					
<p>技术要求:</p> <ol style="list-style-type: none"> 1) 材质: 见附表; 2) 电镀: 见附表; 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象; 4) 端子表面无氧化、电镀不良等现象。 																																																					
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 20%;">2</td> <td style="width: 20%;">PIN</td> <td style="width: 20%;">N PCS</td> <td colspan="3" style="width: 40%;">材质: 黄铜, 电镀: 镀亮锡60u"MIN</td> </tr> <tr> <td>1</td> <td>Housing</td> <td>1 PCS</td> <td colspan="3">材质: PA66 (UL94V-0), 颜色: 本色</td> </tr> <tr> <td>NO.</td> <td>NAME</td> <td>Q'TY</td> <td colspan="3">DESCRIPTION</td> </tr> </table>													2	PIN	N PCS	材质: 黄铜, 电镀: 镀亮锡60u"MIN			1	Housing	1 PCS	材质: PA66 (UL94V-0), 颜色: 本色			NO.	NAME	Q'TY	DESCRIPTION																									
2	PIN	N PCS	材质: 黄铜, 电镀: 镀亮锡60u"MIN																																																		
1	Housing	1 PCS	材质: PA66 (UL94V-0), 颜色: 本色																																																		
NO.	NAME	Q'TY	DESCRIPTION																																																		
 深圳市韩下电子有限公司																																																					
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 20%;">DRAW:</td> <td style="width: 20%;">黄彬</td> <td style="width: 20%;">2020-8-18</td> <td style="width: 20%;">TITLE:</td> <td colspan="3" style="width: 20%;">DRAW NAME:</td> </tr> <tr> <td>DESIGN:</td> <td></td> <td></td> <td>针座</td> <td colspan="3">HX-2510-5AW</td> </tr> <tr> <td>CHECK:</td> <td>张伟</td> <td>2020-8-18</td> <td>SERIES:</td> <td colspan="3">1501 SERIES</td> </tr> <tr> <td>APPROVED:</td> <td>罗小春</td> <td>2020-8-18</td> <td>P/N:</td> <td colspan="3"></td> </tr> <tr> <td colspan="4" style="text-align: center;">CUSTOMER DRAWING</td> <td>REV.</td> <td>1.00</td> <td>SCALE</td> <td>N/A</td> <td>UNIT:</td> <td>mm</td> <td>SHEET:</td> <td>1/1</td> <td></td> </tr> </table>													DRAW:	黄彬	2020-8-18	TITLE:	DRAW NAME:			DESIGN:			针座	HX-2510-5AW			CHECK:	张伟	2020-8-18	SERIES:	1501 SERIES			APPROVED:	罗小春	2020-8-18	P/N:				CUSTOMER DRAWING				REV.	1.00	SCALE	N/A	UNIT:	mm	SHEET:	1/1	
DRAW:	黄彬	2020-8-18	TITLE:	DRAW NAME:																																																	
DESIGN:			针座	HX-2510-5AW																																																	
CHECK:	张伟	2020-8-18	SERIES:	1501 SERIES																																																	
APPROVED:	罗小春	2020-8-18	P/N:																																																		
CUSTOMER DRAWING				REV.	1.00	SCALE	N/A	UNIT:	mm	SHEET:	1/1																																										

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X.		X°.	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	