


使用温度范围 (Ambient temperature Range):	-25°~+85°	孔位	A	B
适用线规 (Applicable Wires):	AWG 28#~20#	2	0	5.4
适用基板厚度 Applicable PCboard thickness):	1.7mm	4	4.2	9.6
额定电压 (Voltage rating):	300V AC,DC	6	8.4	13.8
额定电流 (Current rating):	4A	8	12.6	18.0
接触电阻 Contact Resistance):	<0.015Ω	10	16.8	22.2
绝缘电阻 (Insulation Resistance):	>1000MΩ	12	21.0	26.4
耐压 (Withstand Voltage):	1000V/min	14	25.2	30.6
材料 (Material)		16	29.4	34.8
1.基座: PA66 FV2		18	33.6	39.0
2.插针: 黄铜		20	37.8	43.2
		22	42.0	47.4
		24	46.2	51.6

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENE RL TOLERANCE		制图 DRAWING	黄彬 2021.01.15	料号 PART NO.	HX-5569-2x6A	版本 REV.	A
			X.±0.25	X.±2°	审核 CHECK	张伟 2021.01.15	品名 TITLE	针座	页次 SHEET	1/1
			.X±0.20	.X'±1°	核准 APPROVAL	罗小春 2021.01.15	客户料号 CUTM. NO.			
			.XX±0.15	.XX'±0.5°	单位 UNITS	MM	比例	1:1		
			.XXX±0.10	.XXX'±0.5°						