


General tolerances(mm)														0.1/10
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	±2'



Product model	PIN	A	B	C
ZX-DGRC-5.08-2P-B	2	12.16	5.08	5.08
ZX-DGRC-5.08-3P-B	3	17.24	10.16	10.16
ZX-DGRC-5.08-4P-B	4	22.32	15.24	15.24
ZX-DGRC-5.08-5P-B	5	27.40	20.32	20.32
ZX-DGRC-5.08-6P-B	6	32.48	25.40	25.40
ZX-DGRC-5.08-7P-B	7	37.56	30.48	30.48
.....				
ZX-DGRC-5.08-24P-B	24	5.08xN+2	5.08x(N-1)	5.08x(N-1)

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/15	/	300/10
IEC Standard			
Overvoltage Category/Pollution Degree	Ⅲ/3	Ⅲ/2	Ⅱ/2
Rated Voltage(V)/Current(A)	/	320/20	/
Rate Impulse Voltage(KV)	/	4	/
Pitch(mm)/Poles	5.08/N=02~24P		
Operating temperature(°C)	-40~+105		
Conform to RoHS	Yes		

2	Pin	Copper	Sn Plated
1	Housing	PA66	UL94V-0 Black
ITEM	NAME OF PART	MATERIAL	NOTES

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	Yu			料号 PART NO.	ZX-DGRC-5.08-NP-B	版本 REV.	A						
									审核 CHECK	HUANG			品名 TITLE	Socket-type terminal	页次 SHEET	1/1		
									核准 APPROVAL				RUAN			客户料号 CUTM.NO.		
									单位 UNITS							MM	比例 SCALE	