




电路示意图



推荐插头尺寸

NOTES:

1. VOLTAGE RATING: 30V DC ;
2. CURRENT RATING: 1.5A ;
3. CONTACT RESISTANCE: $\leq 30m\Omega$;
4. INSULATION RESISTANCE: $\geq 100M\Omega$;
5. WITHSTAND VOLTAGE: 500 VAC ;
6. UNMATING FORCE: 3N~30N ;
7. OPERATING LIFE: 5000 CYCLES MIN ;
8. OPERATION TEMPERATURE: $-20^{\circ}C \sim +80^{\circ}C$;



Ordering Information

HC- DC*** - * - * ** - * - * ** - 08

序列号 Nature Foot Type T=Through holes PIN Diameter Material
M=Male 2=2P DP=2P (Holes) 1.3~1.3mm HT=1.0~1.1
F=Female 3=3P SM=3P (Holes) 1.65~1.65mm M=1.0
4=4P VS=Vertical SMT (Holes) 2.0~2.0mm
M=Mid Mount (Holes) 2.5~2.5mm
DS=DP+SMT (Holes)
WB=Wire Bonding (Holes)

6	后盖	黄板	1	黄色
5	主体	PBT UL94V-0	1	黑色
4	平片	黄铜 T=0.3mm	1	镀铜锡
3	弯片	黄铜 T=0.3mm	1	镀铜锡
2	弹片	磷铜 T=0.25mm	1	镀铜锡
1	PIN针	黄铜	1	镀铜锡
序号	名称	材料	数量	颜色/电镀

			GENERAL TOLERANCE		制图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核				
			X.X	± 0.30	批准	产品名称	电源插座 母座 3P 焊线式	版本	A
			X.XX	± 0.20	比例	产品料号	02.0 全铜	REV.	
			X.XXX	± 0.10	SCALE	PART NO.	HC-DC015-F-3WB-2.0-HT-08	单位	mm
1	初版发行	日期	Angle	$\pm 3.0^{\circ}$	投影	材料		页次	1/1
序号	变更内容	MODIFY DATE			Projection	MATERIAL		SHEET	