


1. VOLTAGE RATING: 20V DC ;
2. CURRENT RATING: 5A ;
3. CONTACT RESISTANCE: $\leq 30\text{m}\Omega$;
4. INSULATION RESISTANCE: $\geq 100\text{M}\Omega$;
5. WITHSTAND VOLTAGE: 500 VAC ;
6. UNMATING FORCE: 3N~30N ;
7. OPERATING LIFE: 3000 CYCLES MIN ;
8. OPERATION TEMPERATURE: $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$;



HC- DC*** - * - * ** - * - ** - ** - 08

序列号	Nature	Foot	Type	T=Through holes	Pin Diameter	Material
M=Male	2=2P	DP=DP (插针)				HT=H (铜)
F=Female	3=3P	SMT=SMT (贴片)			1.3#1.3mm	M=1 (铝)
	4=4P	VS=Vertical (立座)			1.65#1.65mm	
		V=Vertical (立座)			2.0#2.0mm	
		MS=MS Mount (立座)			2.5#2.5mm	
		DS=DS=SMT (表面贴片)				
		WB=Wire Bonding (导线线)				

			GENERAL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			X.X	±0.30	批 准 APPROVAL	产品名称 TITLE	电源插座 母座 4P 立插 02.0 全铜	版 本 REV.	A
1	初版发行		X.XX	±0.20		产品料号 PART NO.	HC-DC013L-F-4VD-2.0-HT-08	单 位 UNITS	mm
			X.XXX	±0.10					
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle	±3.0°	投 影 Projection		材 料 MATERIAL	页 次 SHEET	1/1


 深圳市华灿天禄电子有限公司
 ShenzhenhuacantianluELECTRONICS CO.,LTD

产品名称 TITLE	电源插座 母座 4P 立插 Ø2.0 全铜	版 本 REV.	A
产品料号 PART NO.	HC-DC0131-F-4VD-2.0-HT-08	单 位 UNITS	mm
材 料 MATERIAL		页 次 SHEET	1/1