






NOTES:

1. VOLTAGE RATING: 30V DC ;
2. CURRENT RATING: 5A ;
3. CONTACT RESISTANCE: $\leq 30m\Omega$;
4. INSULATION RESISTANCE: $\geq 100M\Omega$;
5. WITHSTAND VOLTAGE: 500 VAC ;
6. UNMATING FORCE: 3N~30N ;
7. OPERATING LIFE: 5000 CYCLES MIN ;
8. OPERATION TEMPERATURE: $-20^{\circ}C \sim +80^{\circ}C$;



Ordering Information

HC- DC*** - * - * ** - * - * ** - ** - 08

序列号	Nature	Foot	Type	T=Through holes	PIN Diameter	Material
M=Male	2=2P	DP=DP (插孔)	VS=Vertical SMT (垂直)	1.3~1.3mm	HT=1.0	
F=Female	3=3P	SM=SMT (贴片)	M=Mid Mount (中装)	1.65~1.65mm	M=1.0	
	4=4P	VS=Vertical SMT (垂直)	DS=DP+SMT (插孔+贴片)	2.0~2.0mm		
		WB=Wire Bonding (引线键合)		2.5~2.5mm		

4	外壳	黄铜H59	1	镀铜锡
3	绝缘体	PA66	1	黑色
2	弹片	磷铜	1	镀铜锡
1	PIN针	黄铜	1	镀铜锡
序号	名称	材料	数量	颜色/电镀

			GENERAL TOLERANCE	制图		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核					
			X.X ±0.30	批准					
			X.XX ±0.20	比例					
			X.XXX ±0.10	SCALE		产品名称	电源插座 母座 2P 焊线式	版本	A
1	初版发行		Angle ±3.0°	投影		产品料号	HC-DC084-F-2WB-2.1-HIT-08	单位	mm
序号	变更内容	日期				PART NO.		页次	1/1
No.	MODIFY CONTENT	MODIFY DATE				MATERIAL		SHEET	