











P.C.B 设计参考尺寸
公差: ±0.05



推荐插头尺寸



电路示意图



RECOMMENDED SMT SOLDERING THERMAL PROFILE

NOTES:

1. VOLTAGE RATING: 30V DC ;
2. CURRENT RATING: 1A ;
3. CONTACT RESISTANCE: $\leq 30m\Omega$;
4. INSULATION RESISTANCE: $\geq 100M\Omega$;
5. WITHSTAND VOLTAGE: 500 VAC ;
6. UNMATING FORCE: 3N~30N ;
7. OPERATING LIFE: 5000 CYCLES MIN ;
8. OPERATION TEMPERATURE: -20°C~+80°C ;



Ordering Information

HC- DC*** - * - * ** - * - ** - ** - 08

序列号 Nature Foot Type T=Through holes PIN Diameter Material
M=Male 2=2P DP=DP (0.8) 1.3~1.3mm HT=1.0
F=Female 3=3P SMT=SMT (0.8) 1.65~1.65mm M=1.0
4=4P VS=Vertical SMT (0.8) 2.0~2.0mm
MM=Mid Mount (0.8) 2.5~2.5mm
DS=DP+SMT (0.8)

6	后盖	LCP UL94V-0	1	黑灰色
5	主体	LCP UL94V-0	1	黑灰色
4	平片	黄铜 T=0.3mm	1	CuSn打底1um, Sn表面0.15um
3	弯片	黄铜 T=0.3mm	1	
2	弹片	磷铜 T=0.3mm	1	
1	PIN针	黄铜	1	
序号	名称	材料	数量	颜色/电镀

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
					DRAWING				
			DIM	TOL	审 核	产品名称	电源插座 母座 3P 卧插	版 本	A
			X.X	±0.30	CHECK	TITLE	02.0 全铜	REV.	
			X.XX	±0.20	批 准	产品料号	HC-DC2526-F-3DIP-2.0-HT-08	单 位	mm
			X.XXX	±0.10	APPROVAL	PART NO.		页 次	1/1
			Angle	±3.0°	比 例	材料		SHEET	
					SCALE	MATERIAL			
1	初版发行	日期			投影				
序号	变更内容	MODIFY DATE							
No.	MODIFY CONTENT								