




General tolerances(mm)														0.1/10
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	±2'



Product model	PIN	A	B	C
ZX-DGVC-3.81-2P-B	2	3.81	8.41	3.81
ZX-DGVC-3.81-3P-B	3	7.62	12.22	7.62
ZX-DGVC-3.81-4P-B	4	11.43	16.03	11.43
ZX-DGVC-3.81-5P-B	5	15.24	19.84	15.24
ZX-DGVC-3.81-6P-B	6	19.05	23.65	19.05
ZX-DGVC-3.81-7P-B	7	22.86	27.46	22.86
.....				
ZX-DGVC-3.81-24P-B	24	3.81x(N-1)	3.81xN+0.79	3.81x(N-1)

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/8	/	300/8
IEC Standard			
Overvoltage Category/Pollution Degree	Ⅱ/2		
Rated Voltage(V)/Current(A)	250/7		
Rate Impulse Voltage(KV)	2.5		
Pitch(mm)/Poles	3.81/N=02~24P		
Operating temperature(°C)	-40~+105		
Conform to RoHS	Yes		

2	Pin	Copper alloy	Sn Plated
1	Housing	PA66	UL94V-0 Black
ITEM	NAME OF PART	MATERIAL	NOTES

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	Yu			料号 PART NO.	BX-DGVC-3.81-NP-B	版本 REV.	A
					审核 CHECK	HUANG			品名 TITLE	Socket-type terminal	页次 SHEET	1/1
					核准 APPROVAL	RUAN			客户料号 CUTM.NO.			
					单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)			