


P. C. B 设计参考尺寸

NOTES:

1. VOLTAGE RATING: 30V DC ;
2. CURRENT RATING: 0.5A ;
3. CONTACT RESISTANCE:  $\leq 30m\Omega$  ;
4. INSULATION RESISTANCE:  $\geq 100M\Omega$  ;
5. WITHSTAND VOLTAGE: 500 VAC ;
6. UNMATING FORCE: 3N~30N ;
7. OPERATING LIFE: 5000 CYCLES MIN ;
8. OPERATION TEMPERATURE:  $-20^{\circ}C \sim +80^{\circ}C$  ;



Ordering Information

HC- DC\*\*\* - \* - \* \*\* - \* - \*\* - \*\* - 08

序号号	Nature M=Male F=Female	Foot 2=2P 3=3P 4=4P	Type DP=DIP (插孔) SM=SMT (贴片) V=Vertical DP (垂直)	T=Through holes	PIN Diameter 1.25±0.2mm 1.65±0.15mm 2.0±0.2mm 2.5±0.25mm	Material HT=HT M=HT
-----	------------------------------	------------------------------	--	-----------------	--	---------------------------

5	主体	PA9T	1	黑色
4	平片	黄铜 T=0.3mm	1	镀银
3	弯片	黄铜 T=0.3mm	1	镀银
2	弹片	磷铜 T=0.25mm	1	镀银
1	PIN针	黄铜	1	镀铜锡
序号	名称	材料	数量	颜色/电镀

		GENERAL TOLERANCE		制图	
		DIM	TOL	审核	
		X.X	±0.30	批准	
		X.XX	±0.20	比例	
		X.XXX	±0.10	投影	
		Angle	±3.0°		
1	初版发行				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE			

深圳市华灿天禄电子有限公司  
ShenzhenhuacantianluELECTRONICS CO., LTD

产品名称 TITLE	电源插座 母座 4P 卧插 01.3 全铜	版本 REV.	A
产品料号 PART NO.	HC-DC033-F-4DIP-1.3-HT-08	单位 UNITS	mm
材料 MATERIAL		页次 SHEET	1/1