



电路示意图



推荐插头尺寸



P.C.B 设计参考尺寸

1. VOLTAGE RATING: 24V DC ;
2. CURRENT RATING: 3A ;
3. CONTACT RESISTANCE: $\leq 30\text{m}\Omega$;
4. INSULATION RESISTANCE: $\geq 100\text{M}\Omega$;
5. WITHSTAND VOLTAGE: 500 VAC ;
6. UNMATING FORCE: 3N~30N ;
7. OPERATING LIFE: 5000 CYCLES MIN ;
8. OPERATION TEMPERATURE: $-20^{\circ}\text{C}\sim+80^{\circ}\text{C}$;



Ordering Information

HC- DC*** - * - * ** - * - ** - ** - 08

Order No.	Nature	Foot	Type	T=Through holes	PIN Diameter	Material
M=Male	2=2P	DiP=DiP (直插)	VS=Vertical DIP (直插)	1.25±0.15mm	H=1.5mm	
F=Female	3=3P	SMT=SMT (贴片)	VD=Vertical SMT (贴片)	2.0±0.15mm		
	4=4P		M=Mid Mount (中装)	2.5±0.25mm		
			DS=DiP+SMT (直插贴片)			
			WB=Wire Bonding (线绕式)			

5	外壳	黄铜	1	镀镍
4	弹片	磷铜	1	镀银
3	静片	黄铜	1	镀银
2	PIN针	H59	1	镀银
1	主体	PPA	1	黑色
序号	名称	材料	数量	颜色/电镀

			GENERAL TOLERANCE	制 图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD				
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL		产品名称 TITLE	电源插座 母座 5P 沉板 Ø1.65 全铜	版 本 REV.	A
1	初版发行		X.XX ±0.20	比 例 SCALE		产品料号 PART NO.	HC-DC023D-F-5MM-1.65-HT-08	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX ±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°						

