





PIN	Ø3.0	Ø2.5
APPO		



电路示意图




推荐插头尺寸



P.C.B 设计参考尺寸

NOTES:

1. VOLTAGE RATING: 30V DC ;
2. CURRENT RATING: 0.5A ;
3. CONTACT RESISTANCE: $\leq 30m\Omega$;
4. INSULATION RESISTANCE: $\geq 100M\Omega$;
5. WITHSTAND VOLTAGE: 500 VAC ;
6. UNMATING FORCE: 3N~30N ;
7. OPERATING LIFE: 5000 CYCLES MIN ;
8. OPERATION TEMPERATURE: $-20^{\circ}C \sim +80^{\circ}C$;



Ordering Information

HC- DC*** - * - * ** - * - ** - ** - 08

序号	Nature	Foot	Type	T=Through holes	PIN Diameter	Material
M=Male	F=Female	2=2P 3=3P 4=4P	DP=DP (直插) SM=SMT (贴片) VS=Vertical SMT (垂直贴片) MM=Mid Mount (中插) DS=DP+SMT (直插贴片) WB=Wire Bonding (导线键合)		1.3~1.3mm 1.65~1.65mm 2.0~2.0mm 2.5~2.5mm	HT=HT M=M

6	后盖	PBT UL94V-0	1	黑色
5	主体	PBT UL94V-0	1	黑色
4	平片	黄铜 T=0.5mm	1	AG/CuSn-0.15um
3	弯片	黄铜 T=0.5mm	1	
2	弹片	磷铜 T=0.25mm	1	
1	PIN针	黄铜H65	1	CuSn-0.15um
序号	名称	材料	数量	颜色/电镀

			GENERAL TOLERANCE	制图		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核					
			X.X ±0.30	批准		产品名称	电源插座 母座 3P 卧插	版本	A
			X.XX ±0.20	CHECK		TITLE	02.5/03.0 全铜	REV.	
			X.XXX ±0.10	APPROVAL		产品料号	HC-DC062-F-3DIP-XX-HT-08	单位	mm
			Angle ±3.0°	比例		PART NO.		页次	1/1
1	初版发行			投影		材料		SHEET	
序号	变更内容	日期		投影		MATERIAL			
No.	MODIFY CONTENT	MODIFY DATE		Projection					