

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	
A1	N/A		图面升级整理图面	2024.08.29


- SPECIFICATIONS
- Voltage rating:50V AC/DC
 - Current rating:1A AC/DC
 - Withstanding Voltage:500V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥100MΩ
 - Contact resistance:≤20mΩ

PART NO.:

X1011 W V S-2xXX S-9T XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 1.Series No
2.Category:W-Wafer
3.Welding Board Angle:V-Stright 180°
4.WELDING Way:S-SMT
5.Row No.Pin No:2xXX-2x02~2x25Pin
6.Special No:S-Positioning coulumn
7.Material:9T-PA9T UL94V-0
8.Plating:SN-Bright tin plating
V01-All Gold Flash

Poles	Dimensions/mm				Poles	Dimensions/mm			
	A	B	C	D		A	B	C	D
2x02	1.00	4.30	2.50	麦拉	2x11	10.00	13.30	11.50	7.00
2x03	2.00	5.30	3.50		2x12	11.00	14.30	12.50	
2x04	3.00	6.30	4.50		2x14	13.00	16.30	14.50	
2x05	4.00	7.30	5.50		2x15	14.00	17.30	15.50	
2x06	5.00	8.30	6.50		2x16	15.00	18.30	16.50	
2x07	6.00	9.30	7.50	4.00	2x18	17.00	20.30	18.50	
2x08	7.00	10.30	8.50		2x20	19.00	22.30	20.50	
2x09	8.00	11.30	9.50		2x25	24.00	27.30	25.50	
2x10	9.00	12.30	10.50	7.00					
X1011WVS-2xXXS-9TV01		PA9T UL 94V-0		Phosphor Bronze		X1011T			
PART NO		Material		Material(Pin And Solder Tabs)		Suitable XKB Housing			



ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	1.0mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X1011WVS-2xXXS-9TV01
APPROVED		SIZE:	A4	DWG NO.:	

SCALE	PAGE	REVISION
N/A	1/1	A1