




标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE
PIN 数	A±0.15	B±0.15	C±0.15	D±0.15
9P	11.30	8.00	10.25	9.65
10P	12.30	9.00	11.25	10.65
11P	13.30	10.00	12.25	11.65
12P	14.30	11.00	13.25	12.65
13P	15.30	12.00	14.25	13.65
14P	16.30	13.00	15.25	14.65
15P	17.30	14.00	16.25	15.65
16P	18.30	15.00	17.25	16.65

Specifications:
1.Rated Voltage : 50V AC/DC
2.Rated Current : 1A AC,DC
3.Withstand Voltage : 200V AC/minute
4.Contact Resistance : 50mΩ(MAX.)
5.Insulation Resistance : 100MΩ(MIN.)
6.Storage Temperature Range: -40℃~+85℃;
7.Operation Temperature Range: -25℃~+70℃;

2	插针	铜	镀镍锡	
1	基座	LCP	本色	
序 号	品 名	材 质	电镀/颜色	备 注

	品 名 TITLE 料 号 PART NO		针座 HCZZ0039-15	
UNLESS OTHERWISE, GENERAL TOLERANCE:		比 列 SCALE	1:1	
X. xxx ±0.05 X. xx ±0.15 X. x ±0.25		单 位 UNIT	MM	
ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°		张 数 PART NO	1 OF 1	
		版 本 REV	A	
		制 图 DRAW	AhYe	
		审 核 CHECKED	夏操云	
		批 准 APPROVE	赵亮亮	