


Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ MAX

接触电阻: ≤20mΩ MAX

X1270 H I -2xXX - PT V01

① ②③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:H- HSG
- 3.Welding Board Angle:I-HSG+hardware
- 4.Row No-Pin No:2xXX-2x03P~2x25P
- 5.Material:PT-PBT UL94V-0
- 6.Plating:V01-All Gold Flash

NUMBER OF POSITIONS	DIMENSION		NUMBER OF POSITIONS	DIMENSION	
	A	B		A	B
2x03	8.00	2.54	2x13	20.70	15.24
2x04	9.27	3.81	2x15	23.24	17.78
2x05	10.54	5.08	2x17	25.78	20.32
2x06	11.81	6.35	2x20	29.59	24.13
2x07	13.08	7.62	2x22	32.13	26.67
2x08	14.35	8.89	2x25	35.94	30.48
2x10	16.89	11.43	2x30	44.29	36.83
2x12	19.43	13.97	2x32	44.83	39.37

X1270HI-2xXX-PTV01	PBT	Brass	XPD0.635-A28PXX-IDC	X1270H-2xXX
				X1270HI-2xXX
PART NO	Material	Material(pin)	Suitable XKB flat cable	Suitable XKB IDC

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	1.27mm DIP
CHKD		UNIT: mm/in	PART NO.: X1270HI-2xXX-PTV01
APPD		SIZE: A4	DWG NO.: X-X1270HI-2xXX-PTV01
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT
			SHEET
			REVISION
			1/1
			A0