








10P以下
无此凸台

**Specifications:****规格:****Voltage rating:**100V AC/DC**额定电压:** 100V AC/DC**Current rating:**2A AC/DC**额定电流:** 2A AC/DC**Withstanding voltage:**500V AC/minute**耐受电压:** 500V AC/分钟**Temperature range:**-40℃~+85℃**温度范围:** -40℃~+85℃**Insulation resistance:**≥500MΩ**绝缘电阻:** ≥500MΩ**Contact resistance:**≤20mΩ**接触电阻:** ≤20mΩ

X1507 H - XX N0
① ② ③ ④


1.Series Number**2.Category:**H-HSG**3.Row No.Pin No.:**xx-02-16P**4.Material:**N0-PA66 94V-0

Poles	Dimensions (mm)				Poles	Dimensions (mm)			
	A	B	C	D		A	B	C	D
02	1.50	5.00	3.60	2.70	10	13.50	16.80	15.60	9.80
03	3.00	6.30	5.10	3.45	11	15.00	18.30	17.10	9.80
04	4.50	7.80	6.60	4.45	12	16.50	19.80	18.60	9.80
05	6.00	9.30	8.10	4.45	13	18.00	21.30	20.10	11.30
06	7.50	10.80	9.60	7.45	14	19.50	22.80	21.60	11.30
07	9.00	12.30	11.10	7.45	15	21.00	24.30	23.10	11.30
08	10.50	13.80	12.60	9.80	16	22.50	25.80	24.60	11.30
09	12.00	15.30	14.10	9.80					

X1507H-XX-N0	PA66 UL 94V-0	X1507T	X1507W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

ΔX					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB	DSND		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connector
	DWN		VIEW:	PART NO.: X1507H-XX-N0
	CHKD		UNIT: mm/in	DWG NO.: X-X1507H-XX-N0
	APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0
XKB INDUSTRIAL PRECISION CO.,LIMITED				




2P

3P

4P

5P


6P



7P

8P

9P



11P

12P-13P

14P-16P

							DSND		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connector			
					ANGLAR	±5°		DWN	VIEW: 	PART NO.: X1507H-XX-N0			
ΔX					L ≤ 4	±0.2		CHKD	UNIT: mm/in	DWG NO.: X-X1507H-XX-N0			
ΔX					4<L ≤ 16	±0.3		APPD	SIZE: A4				
ΔX					16<L ≤ 63	±0.4							
MARK	DESCRIPTION		DATE	REVISED	APPROVED	L > 63	±0.5				WEIGHT	SHEET	REVISION
REVISIONS							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn													