








Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)



P = With Post



默认= W/O Post

#### SPECIFICATIONS

Rated Current:1.0AMP  
Contact Resistance:20mΩ Max  
Withstand Voltage:500V AC/DC  
Insulation Resistance:1000MΩ Min  
Operation Temperature:-40°C to +105°C

Contact Material:Brass  
Contact Plating:Au or Sn Over Ni  
Insulator Material:Polyester(UL94V-0)  
Standard: PA6T  
Max.Processing Temp: 230°C for 30-60 seconds  
(260°C for 10 seconds)

| Pitch  | 塑高变量 (mm) |
|--------|-----------|
| 1.27mm | 0.85      |
|        | 1.0       |
|        | 1.5       |
|        | 1.7       |
|        | 2.0       |
|        | 2.5       |

#### Dimension antitheses list

| ITEM     | PA   | PB   | W    | L    |
|----------|------|------|------|------|
| Standard | 3.80 | 2.50 | 5.50 | 6.30 |

#### Ordering Information

PZ 127 - \* - N - \* - \* - \*\* - \* - P

No. of Rows  
1=Single Row  
2=Dual Row

No. of Pins  
2=20Pin  
2-50Pin

Type  
S=Single  
D=Dual

Length  
(mm)

Contact Plating  
G0:Gold Flash  
G1:1u" Gold  
G2:3u" Gold  
G3:5u" Gold  
G4:10u" Gold  
G5:15u" Gold  
G6:30u" Gold  
S0:Gold Flash/Tin  
S1:Tin

Packing  
R=Reel  
+Cap  
(编带+盖)

Post  
(带柱)

|     |                |             |                   |       |            |                                                           |                      |       |     |
|-----|----------------|-------------|-------------------|-------|------------|-----------------------------------------------------------|----------------------|-------|-----|
|     |                |             | GENERAL TOLERANCE |       | 制 图        | 深圳市华灿天禄电子有限公司<br>ShenzhenhuacantianluELECTRONICS CO., LTD |                      |       |     |
|     |                |             | DIM               | TOL   | DRAWING    |                                                           |                      |       |     |
|     |                |             | X. X              | ±0.30 | 审 核        | 产品名称                                                      | 1.27 双排 排针 贴片 编带+盖   | 版本    | A   |
|     |                |             | X. XX             | ±0.20 | CHECK      | TITLE                                                     | (塑高2.0)              | REV.  |     |
|     |                |             | X. XXX            | ±0.10 | 批 准        | 产品料号                                                      | PZ127-2-N-S-2.0-XX-R | 单 位   | mm  |
|     |                |             | Angle             | ±3.0° | APPROVAL   | PART NO.                                                  |                      | 页 次   | 1/1 |
| 序号  | 变更内容           | 日期          |                   |       | 比 例        | 材 料                                                       |                      | SHEET |     |
| No. | MODIFY CONTENT | MODIFY DATE |                   |       | SCALE      | MATERIAL                                                  |                      |       |     |
|     |                |             |                   |       | 投影         |                                                           |                      |       |     |
|     |                |             |                   |       | Projection |                                                           |                      |       |     |