






VOLTAGE: 125 VOLTS AC.
CURRENT RATING : 1.5AMP.
DIELECTRIC STRENGTH: 1000 VAC RMS 50HZ OR 60HZ,1MIN.
INSULATION RESISTANCE: 500 MEGA OHMS MIN. INITIAL
AFTER 500V DC FOR 1 MINUTE.
CONTACT RESISTANCE: SINGLE TERMINAL 30 MILLIOHMS MAX.
INITIAL 50 MILLIOHMS MAX. AFTER
DURABILITY TEST.

PORTS	N	A $\pm$ 0.25	B $\pm$ 0.25	C $\pm$ 0.05
2x8	7	113.82	130.95	113.82
2x6	5	81.30	98.43	81.30
2x4	3	48.78	65.91	48.78
2x3	2	32.52	49.45	32.52
2x2	1	16.26	33.39	16.26

Standard LED Color	LED Wavelength	Foward(A)	Foward(V)
Yellow	568nm	20mA	1.85-2.45
Green	585nm	20mA	1.7-2.2V

Ordering Information



			GENERAL TOLERANCE	制 图 DRAWING	04	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK					
			X. X ± 0.30	批 准 APPROVAL		产品名称 TITLE	网络插座 (双层4口 卧插 带灯带弹 左绿右绿)	版 本 REV.	A
1	初版发行		X. XX ± 0.20	比 例 SCALE		产品料号 PART NO.	HC-RJ45-059C-2*4-1-2T	单 位 UNITS	mm
			X. XXX ± 0.10						
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ± 3.0°	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1