

6
注：未经允许禁止传输、复制、编辑该文档，以及利用其内容进行交流。

D

C

B

REV E.C.N NO. CONTENT CHK DATE

NOTES1:
UL Standard

1.

Use group	B	C	D
Rated Current	8A	8A	8A
Rated Voltage	150V	50V	150V

2.Wire range: 24~16AWG

IEC Standard

1.

Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
Rate Voltage(V)	160V	160V	250V
Rate Current(A)	8A	8A	8A

2.wire range: 0.2~1.5mm²

NOTES2:

1.Housing: PA66 (UL94V-0)
2.Cover: PA66 (UL94V-0)
3.Button: POM
4.Conductor: Copper alloy (Sn Plated)
5.Spring: Stainless Steel

NOTES3:

1.Pitch: 3.5mm Poles: 2x(02-24)P
2.Stripping length: 9-10mm
3.Operating temperature: -40℃~+105℃
4.RoHS Compliance

How to order

MX15EDGKNH - 3.5 - 2×XXP - XXXX - X - X

产品型号 间距 极数 颜色: 01:常规颜色 A-Z其他定制

灰色:GY 橙色:OE 02-99: 定制颜色
蓝色:BU 红色:RD
黑色:BK 透明色:TT Cu:铜
绿色:GN 黄色:YW Fe:铁
白色:WE

Pitch Range In mm		Nominal Dimension Range In mm							-	∩	◇
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10			
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°			

ITEM NAME OF PART NO. OF PART Q'TY MATERIAL NOTE

DWG. CKK DATE 23.06.20 UNITS MM SHEET/OF 1/1

CHK. DATE SCALE 1:1 A4

APP. DATE NAME MX15EDGKNH-3.5-2×XXP DWGNO.

CIXI MAIXU ELECTRONICS CO.,LTD.
慈溪市迈旭电子有限公司

REV	E.C.N NO.	CONTENT	CHK	DATE

NOTES1:

UL Standard

1.

Use group	B	C	D
Rated Current	8A	8A	8A
Rated Voltage	150V	50V	150V

2.Wire range: 24~16AWG

IEC Standard

1.

1. Pollution Degree	3	2	2
Overvoltage Category	III	II	I
Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
Rate Voltage(V)	160V	160V	250V
Rate Current(A)	8A	8A	8A

2.wire range: $0.2 \sim 1.5 \text{ mm}^2$

NOTES2:

1.Housing: PA66 (UL94V-0)

2.Cover: PA66 (UL94V-0)

3.Button: POM

4. Conductor: Copper alloy (Sn Plated)

5.Spring: Stainless Steel

NOTES3:

1.Pitch: 3.5mm Poles: 2x(02-24)P

2.Stripping length: 9-10mm

3.Operating temperature: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$

4.RoHS Compliance

How to order

MX15EDGKNH - 3.5 - 2×XX - XXXX - X - X

产品型号 间距 极数 颜色: 01:常规颜色 A-Z其他定制

灰色:GY 橙色:OE 02-99:
蓝色:BU 红色:RD 定制颜色
黑色:BK 透明色:TT
绿色:GN 黄色:YW
白色:WE

Cu:铜
Fe:铁

Pitch Range In mm			Nominal Dimension Range In mm					—		
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°		

ITEM	NAME OF PART		NO. OF PART	Q"TY	MATERIAL		NOTE	
DWG.	CKK	DATE	23.06.20	UNITS	MM	SHEET/OF	1/1	A
CHK.		DATE		SCALE	1:1	A4		
APP.		DATE		NAME	MX15EDGKNH-3.5-2xXXP			
 CIXI MAIXU ELECTRONICS CO., LTD. 慈溪市迈旭电子有限公司				DWGNO.				